




Safety by Design

Presents

“SCA 1”

Headlamp Alignment System

ISO Color



You are now
entering the

**High
Intensity
Zone**

"SCA 1"

ISO Color




Old Technology

verses

Symtech

ISO Color

Technology



HeadLamp Alignment Procedure

1. Position "SCA 1" in front of First Lamp to be Aligned.
2. Adjust Floor Slope to Recorded Bay Setting.
3. Square "SCA 1" to Vehicle by Looking Through Sighting Unit.
4. Align Two Common Points on Front of Vehicle With Line in Sighting Unit.
5. Select Lamp Beam Type. While viewing Lamp Pattern, Adjust Lamp to Pictorial Position.
6. Move "SCA 1" to Next Lamp and Repeat Steps 3 through 5.

- ISO Color Technology
- Durable and Lightweight
- Adjustable Height
- Laser Floor Slope
- Field Calibration
- Accurate/Repeatable
- Compact and Portable
- Non-Electronic
- Rotational Mast

COLORIZED HEADLAMP PATTERN TECHNOLOGY MAKES HEADLAMP ALIGNMENT FAST AND SIMPLE.



Experiencing
the **High Intensity Zone**
everyday,
is now a
reality

Symtech Corporation
524 S.E. Transport Drive
Lee's Summit, MO 64081

Phone: 1-888-884-8182
Email: info@symtechcorp.net
www.symtechcorp.net

